

# AM4013MZT4

**Značka:**

**Kód produktu:** AM4013MZT4



## Short Description

1.3 Megapixel resolution  
Robust metal housing  
400-470x magnification  
Polarizer (anti-reflection)

## Popis

The AM4013MZT4 with a high magnification of 400~470x reveals even the smallest details on all kinds of objects. The built-in, switchable polarizer makes the AM4013MZT4 the right choice for working with high glare materials such as jewelry, plastics and metals. The aluminum housing offers enhanced protection and durability and has the best look and feel.



USB 2.0



Measurement  
functionality



Adjustable  
~400x-470x



1,3 Megapixels  
1280 x 1024



8 White LEDs  
switchable



Metal  
housing



Standard working distance



Polarizer anti-reflection

## Working distance/field of view/depth of field

MAGNIFICATION RATE	WORKING DISTANCE	FIELD OF VIEW(X)	FIELD OF VIEW(Y)	DEPTH OF FIELD
<b>Listed values may differ slightly</b>				<b>Unit = mm</b>
430	-0.45	0.91	0.73	0.1
440	0.4	0.89	0.71	0.1
450	1.35	0.87	0.7	0.1
460	2.3	0.85	0.68	0.1
470	3.15	0.83	0.67	0.1

## Specifications

<b>Lighting</b>	
Light/ LED type	White
Number of LEDs	8
LED on/off switchable:	Yes
Infrared filter	IR cut-filter >650 nm
Diffuser available	No
Emission filter	No
Polarizer	Yes, linear
<b>Optics</b>	
Magnification	400-470x
Macro zoom	No
Working distance	Standard
Lens type	Glass with anti-reflection coating
<b>Sensor</b>	
Sensor type	CMOS
Resolution	1.3 Megapixel (1280x1024)
Maximum frame rate	30 fps
<b>Compatibility</b>	
Interface	USB 2.0
Operating system	Windows 7,8,10 & 11, MacOS 10.9 and up

Software	DinoCapture 2.0 (Windows), DinoXcope (Mac OS)
Supported image formats (Windows)	BMP, GIF, PNG, JPG, TIF, RAS, PNM, TGA, PCX, MNG, WBMP, JP2, JPC, PGX
Supported video formats (Windows)	WMV, FLV, SWF
Supported image formats (MacOS)	JPEG, PNG
Supported video formats (MacOS)	MOV
Imaging standards	DirectShow, UVC
Wifi	Wireless-ready, requires the WF-10 WiFi streamer (optional)
<b>Housing</b>	
Housing material	Metal housing
Magnification lock	No
Dimensions	10.5cm (L) x 3.2cm (D)
Weight	105g
Cable length	1.8m
<b>Features</b>	
Special feature	No
Measurement	Yes
Calibration	Yes
Microtouch sensor	Yes
ESD safe	Yes
<b>Information</b>	
Package contents	Microscope, carry pouch, software CD, calibration target, ZT-Z-CC1 cap closure, user manual
Warranty information	2 years European warranty
Regulatory approval	CE, FCC, ROHS
Price range	€600,00 - €800,00

## Product Gallery