

# MSAK810



**Marke:** Dino-Lite  
**Artikelnummer:** MSAK810

## Short Description

Flexible extension arm

## Beschreibung

The MSAK810 adjustable flex arm which can be attached to the pole of a RK-06A/RK-06AE/RK-06F for additional hands free viewing angles with the Dino-Lite. The arm has a maximum of 30cm reach, and can be bent and twisted to attain your desired viewing positions.

The MSAK810 is a great addition to a RK-06A/RK-06AE/RK-06F allowing an in-depth visual inspection with multiple Dino-Lite's.

## Spezifikation

Compatibility	
Compatible with:	All Dino-Lite models
Housing	
Dimensions	35.5cm (W) x 3.1cm (L)
Weight	181 g
Features	
ESD safe	No
Information	
Package contents	Stand, HD-P1 holder

Warranty information	2 years European warranty
Accessory range:	Professional stands
Price range	€50,00 - €150,00

## Product Gallery

