

# AF3113T

**Marca:** Dino-Lite  
**Codice del prodotto:** AF3113T



## Short Description

640x480 Resolution  
8 white LEDs (switchable)  
10-70, 200x magnification  
Measurement functionality  
Wireless ready

## Descrizione

The AF3113T has both the measurement functions and the Microtouch button to capture pictures directly from the Dino-Lite. The improved image sensor provides a high quality image with very natural colors and it also offers a high refresh rate for better real time images. It is an affordable solution for industrial, scientific and business use.



USB 2.0



Adjustable  
~10-70x & 200x



Measurement  
functionality



VGA resolution  
640 x 480



8 White LEDs  
switchable



Standard working  
distance



Wireless  
Ready

## Working distance/field of view/depth of field

MAGNIFICATION RATE	WORKING DISTANCE	FIELD OF VIEW(X)	FIELD OF VIEW(Y)	DEPTH OF FIELD
<b>Listed values may differ slightly</b>				<b>Unit = mm</b>
20	51.7	21.0	15.7	8
30	24.1	14.0	10.5	4
40	11.0	10.5	7.9	2.5
50	3.8	8.4	6.3	2
60	-0.6	7.0	5.2	-
200	-0.4	2.1	1.6	0.45
210	0.6	2.0	1.5	-
220	1.7	1.9	1.4	-
230	2.8	1.8	1.4	0.42

## Specifiche

<b>Lighting</b>	
Light/ LED type	White
Number of LEDs	8
LED on/off switchable:	Yes
Infrared filter	IR cut-filter >650 nm
Diffuser available	No
Emission filter	No
Polarizer	No
<b>Optics</b>	
Magnification	10-70x, 200x
Macro zoom	No
Working distance	Standard
Lens type	Glass with anti-reflection coating
<b>Sensor</b>	
Sensor type	CMOS
Resolution	VGA (640x480)
Maximum frame rate	30 fps
<b>Compatibility</b>	
Interface	USB 2.0
Operating system	Windows 7, 8, 10 & 11, MacOS 10.9 and up
Software	DinoCapture 2.0 (Windows), DinoXcope (Mac

	OS)
Supported image formats (Windows)	BMP, GIF, PNG, JPG, TIF, RAS, PNM, TGA, PCX, MNG, WBMP, JP2, JPC, PGX
Supported video formats (Windows)	WMV, FLV, SWF
Supported image formats (MacOS)	JPEG, PNG
Supported video formats (MacOS)	MOV
Imaging standards	DirectShow, UVC
Wifi	Wireless-ready, requires the WF-20 adapter (optional)
<b>Housing</b>	
Housing material	Composite/ plastic housing
Magnification lock	No
Dimensions	10.5cm (L) x 3.2cm (D)
Weight	105g
Cable length	1.8m
<b>Features</b>	
Special feature	No
Measurement	Yes
Calibration	Yes
Microtouch sensor	Yes
ESD safe	No
<b>Information</b>	
Package contents	Microscope, Carry pouch, software CD, calibration target, user manual
Warranty information	2 years European warranty
Regulatory approval	CE, FCC, ROHS
Price range	€150,00 - €350,00