

AM4013MTL



Marca: Dino-Lite

Codice del prodotto: AM4013MTL

Short Description

1.3 Megapixel resolution

Robust metal housing

10-90x magnification

Long working distance

Descrizione

Dino-Lite professional model in aluminium alloy housing and long working distance and Microtouch. The aluminium housing offers enhanced protection and durability and has the best look and feel.



USB 2.0



Measurement
functionality



Continuous
~10-90x



1,3 Megapixels
1280 x 1024



8 White LEDs
switchable



Metal
housing



Long working
distance

Working distance/field of view/depth of field

MAGNIFICATI ON RATE	WORKING DISTANCE	FIELD OF VIEW(X)	FIELD OF VIEW(Y)	DEPTH OF FIELD
20	151.0	19.6	15.6	6
30	101.0	13.0	10.4	3.4
40	77.2	9.8	7.8	2.2
50	64.1	7.8	6.3	1.65
60	56.2	6.5	5.2	.
70	51.3	5.6	4.5	.
80	48.3	4.9	3.9	.
90	46.6	4.3	3.5	0.8

**Listed values
may differ
slightly**

Unit = mm

Specifiche

Lighting	
Light/ LED type	White
Number of LEDs	8
LED on/off switchable:	Yes
Infrared filter	IR cut-filter >650 nm
Diffuser available	No
Emission filter	No
Polarizer	No
Optics	
Magnification	10-90x
Macro zoom	No
Working distance	Long
Lens type	Glass with anti-reflection coating
Sensor	
Sensor type	CMOS
Resolution	1.3 Megapixel (1280x1024)
Maximum frame rate	30 fps
Compatibility	
Interface	USB 2.0
Operating system	Windows 7,8,10 & 11, MacOS 10.9 and up
Software	DinoCapture 2.0 (Windows), DinoXcope (Mac OS)
Supported image formats (Windows)	BMP, GIF, PNG, JPG, TIF, RAS, PNM, TGA, PCX, MNG, WBMP, JP2, JPC, PGX
Supported video formats (Windows)	WMV, FLV, SWF
Supported image formats	JPEG, PNG

(MacOS)	
Supported video formats	MOV
(MacOS)	
Imaging standards	DirectShow, UVC
Wifi	Wireless-ready, requires the WF-10 WiFi streamer (optional)
Housing	
Housing material	Metal housing
Dimensions	10.5cm (L) x 3.2cm (D)
Weight	140g
Cable length	1.8m
Features	
Special feature	No
Measurement	Yes
Calibration	Yes
Microtouch sensor	Yes
ESD safe	Yes
Information	
Package contents	Microscope, carry pouch, software CD, calibration target, user manual
Warranty information	2 years European warranty
Regulatory approval	CE, FCC, ROHS
Price range	€350,00 - €550,00

Product Gallery