

# AD4113T-I2V

**Merk:** Dino-Lite  
**Productcode:** AD4113T-I2V



## Korte omschrijving

1.3 Megapixel resolution  
switchable UV/IR LEDs  
20-200x magnification  
With exchangeable caps

## Omschrijving

The AD4113T-I2V features both IR (~940nm) and UV (~395nm) LED lighting in a single device.



USB 2.0



Adjustable  
~20x-220x



Magnification  
lock



Measurement  
functionality



1.3 megapixel  
1280 x 1024



Infrared  
LEDs ~ 940nm



UV-LEDs  
400 nm



Switchable  
UV/IR LEDs



Standard working  
distance



Exchangeable  
cap


Multiple lighting options provide the ability to view magnified objects under normal

external lighting sources such as white light or under near IR, or UV lighting by simply switching from one to the other. The IR can be use in document examination and new enhanced UV system provides improved fluorescence contrasting for use in forensics, biomedical or machine vision applications.

### Working distance/field of view/depth of field

MAGNIFICATION RATE	WORKING DISTANCE	FIELD OF VIEW(X)	FIELD OF VIEW(Y)	DEPTH OF FIELD
<b>Listed values may differ slightly</b>				<b>Unit = mm</b>
20	51.7	25.1	20.1	4
30	24.1	16.8	13.4	2
40	11.0	12.6	10.1	1.6
50	3.8	10.1	8.0	1.17
60	-0.6	8.4	6.7	-
200	-0.4	2.5	2.0	0.28
210	0.6	2.4	1.9	-
220	1.7	2.3	1.8	-
230	2.8	2.2	1.7	-

### Special Light



### Specificatie

Verlichting	
Licht / LED-type	~395 nm UV + ~940 nm Infrared
Aantal leds	4+4
LED aan / uit schakelbaar:	Yes
Infrarood filter	No
Diffusor beschikbaar	No
Emissiefilter	No

Polarisator	No
<b>Optiek</b>	
Vergroting	10-50x 220x
Macro zoom	No
Werkafstand	Standard
Type lens	Glass with anti-reflection coating
<b>Sensor</b>	
Sensortype	CMOS
Resolutie	1.3 Megapixel (1280x1024)
Maximale framesnelheid	30 fps
<b>Compatibiliteit</b>	
Interface	USB 2.0
Besturingssysteem	Windows 7, 8, 10 & 11, MacOS 10.9 and up
Software	DinoCapture 2.0 (Windows), DinoXcope (Mac OS)
Ondersteunde beeldformaten (Windows)	BMP, GIF, PNG, JPG, TIF, RAS, PNM, TGA, PCX, MNG, WBMP, JP2, JPC, PGX
Ondersteunde videoformaten (Windows)	WMV, FLV, SWF
Ondersteunde beeldformaten (MacOS)	JPEG, PNG
Ondersteunde videoformaten (MacOS)	MOV
Beeldvormingsnormen	DirectShow, UVC
Wifi	Wireless-ready, requires the WF-10 WiFi streamer (optional)
<b>Behuizing</b>	
Materiaal van de behuizing	Composite/ plastic housing
Vergrotingsslot	Yes
Afmetingen	10.5cm (L) x 3.2cm (D)
Gewicht	105g
Kabellengte	1.8m
<b>Kenmerken</b>	
Bijzonderheid	No
Meting	Yes
Kalibratie	Yes
Microtouch-sensor	Yes
ESD veilig	No
<b>Informatie</b>	
Inhoud van de verpakking	Microscope, carry pouch, software CD, calibration target, ZT-Z-CC1 cap closure, user manual
Garantie-informatie	2 years European warranty

Regelgevende goedkeuring	CE, FCC, ROHS
Prijsklasse	€400,00 - €600,00

**Product galerij**

