

AF7115MZT

Merk: Dino-Lite
Productcode: AF7115MZT



Korte omschrijving

High Optical Resolution

5.0 Megapixel

Flexible LED Control (FLC)

Adjustable Polarizer

Adaptable Interface

Robust Metal Housing

Omschrijving

AF7115MZT is a 5-megapixel digital microscope offering high-resolution imaging with a 20x ~ 220x magnification. This model has Flexible LED Control (FLC) for maximizing lighting adjustability and a polarizer for reducing unwanted reflections. AF7115MZT is compatible with WF-20, a Wi-Fi streamer.



USB 2.0



Measurement
functionality



Adjustable
~20x-220x



Magnification
lock



Metal
housing



5 megapixel
2592 x 1944



The AF7115MZT is part of the universal range and with its standard working distance and wide magnification range from 20 – 220x, it is suitable for a wide range of applications. Because of the built-in polarization filter this model is ideal when working with shiny or reflective objects such as metal, plastic, glass, jewelry, electronics, etc.

The main features of the AF7115MZT are:

- 5 Megapixel Edge sensor
- 20-220x magnification
- Integrated polarizer
- Aluminum housing
- Flexible LED Control (FLC)
- Extensive measurement functions
- Calibration
- Exchangeable front caps
- Wireless ready
- And more...

Optical Data Table

MAGNIFICATION RATE	WORKING DISTANCE 1	FIELD OF VIEW(X)	FIELD OF VIEW(y)	DEPTH OF FIELD
10	142.6	39.6	29.7	26.0
20	60.1	19.8	14.8	7.0
30	33.6	13.2	9.9	3.3
40	21.0	9.9	7.4	2.0
50	14.0	7.9	5.9	1.4
60	9.8	6.6	4.9	1.0
70	7.3	5.7	4.2	0.8
80	5.7	4.9	3.7	0.6
90	4.8	4.4	3.3	0.5
100	4.3	4.0	3.0	0.4
110	4.2	3.6	2.7	0.4
120	4.3	3.3	2.5	0.3
130	4.7	3.0	2.3	0.3

140	5.2	2.8	2.1	0.3
150	5.8	2.6	2.0	0.3
160	6.5	2.5	1.9	0.2
170	7.3	2.3	1.8	0.2
180	8.1	2.2	1.6	0.2
190	9.1	2.1	1.6	0.2
200	10.0	2.0	1.5	0.2
210	11.0	1.9	1.4	0.2
220	12.1	1.8	1.3	0.2
Listed values may differ slightly		* Without front cap		Unit = mm

Specificatie

Verlichting	
Licht / LED-type	White
Aantal leds	8
LED aan / uit schakelbaar:	Yes
Infrarood filter	IR cut-filter >650 nm
Diffusor beschikbaar	Yes (N3C-D included)
Emissiefilter	No
Polarisator	Yes, linear
Optiek	
Vergroting	20-220x
Macro zoom	No
Werkafstand	Standard
Type lens	Glass with anti-reflection coating
Sensor	
Sensortype	CMOS
Resolutie	5 Megapixel (2592x1944)
Maximale framesnelheid	30 fps
Compatibiliteit	
Interface	USB 2.0
Besturingssysteem	Windows 7, 8, 10 & 11, MacOS 10.9 and up
Software	DinoCapture 2.0 (Windows), DinoXcope (Mac OS)
Ondersteunde beeldformaten (Windows)	BMP, GIF, PNG, JPG, TIF, RAS, PNM, TGA, PCX, MNG, WBMP, JP2, JPC, PGX

Ondersteunde videoformaten (Windows)	WMV, FLV, SWF
Ondersteunde beeldformaten (MacOS)	JPEG, PNG
Ondersteunde videoformaten (MacOS)	MOV (max 1.3MP)
Beeldvormingsnormen	DirectShow, UVC
Wifi	Wireless-ready, requires the WF-20 (optional)
Behuizing	
Materiaal van de behuizing	Metal housing
Afmetingen	11.5cm (L) x 3.4cm (D)
Gewicht	97gr
Kabellengte	1.8m
Kenmerken	
Bijzonderheid	Flexible LED Control (FLC)
Meting	Yes
Kalibratie	Yes
Microtouch-sensor	Yes
ESD veilig	Yes
Informatie	
Inhoud van de verpakking	Microscope, carry pouch, software CD, calibration target, user manual, N3C-O- Open cap, N3C-C- Closed cap, N3C-D- diffuser cap, N3c-extension cap, N3C-L- Long cap, N3C-S- Side light cap
Garantie-informatie	2 years European warranty
Regelgevende goedkeuring	CE, FCC, ROHS
Prijsklasse	€900,00 - €1100,00