

# AF4535ZTLE


**Merk:****Productcode:** AF4535ZTLE**Korte omschrijving**

1.3 Megapixel Edge sensor  
10x~200x magnification  
Flexible LED Control (FLC)  
Automatic Magnification Reading (AMR)  
Wireless-ready

**Omschrijving**

The Dino-Lite AF4535ZTLE is part of Long Working Distance (LWD) series and connects to your device via USB. The AF4535ZTLE is Wireless-ready, but requires the (optional) WF-20 to make it a fully wireless solution.

In comparison, the AF4x35 series provides a similar working distance range but achieves higher magnifications compared to the AM4x15 series.



---

The AF4535ZTLE is equipped with premium features such as Flexible LED control (FLC), integrated polarizer, extensive measurement functionality and Automatic Magnification Reading (AMR) for measurement-intensive applications.

**The main features of the AF4535ZTLE are:**

- 1.3 Megapixel Edge sensor
- 10x~200x magnification
- Adjustable polarizer
- Automatic Magnification Reading (AMR)
- Flexible LED Control (FLC)
- Wireless-ready, requires the F-20 adapter (optional)
- And more...

**Working distance/field of view/depth of field**

| Magnification Rate                       | Working Distance *         | Field of View(x) | Field of View(y) | Depth of Field   |
|--|----------------------------|------------------|------------------|------------------|
| <b>Listed values may differ slightly</b> | <b>* Without front cap</b> |                  |                  | <b>Unit = mm</b> |
| 10                                       | 355.8                      | 39.1             | 29.3             | 55.2             |
| 20                                       | 173.0                      | 19.5             | 14.7             | 14.5             |
| 30                                       | 113.1                      | 13.0             | 9.8              | 6.7              |
| 40                                       | 83.8                       | 9.8              | 7.3              | 3.9              |
| 50                                       | 66.8                       | 7.8              | 5.9              | 2.6              |
| 60                                       | 55.9                       | 6.5              | 4.9              | 1.9              |
| 70                                       | 48.6                       | 5.6              | 4.2              | 1.5              |
| 80                                       | 43.4                       | 4.9              | 3.7              | 1.2              |
| 90                                       | 39.8                       | 4.3              | 3.3              | 1.0              |
| 100                                      | 37.1                       | 3.9              | 2.9              | 0.8              |
| 110                                      | 35.2                       | 3.6              | 2.7              | 0.7              |
| 120                                      | 33.8                       | 3.3              | 2.4              | 0.6              |
| 130                                      | 32.9                       | 3.0              | 2.3              | 0.5              |
| 140                                      | 32.3                       | 2.8              | 2.1              | 0.5              |
| 150                                      | 32.0                       | 2.6              | 2.0              | 0.4              |
| 160                                      | 31.8                       | 2.4              | 1.8              | 0.4              |
| 170                                      | 31.9                       | 2.3              | 1.7              | 0.4              |
| 180                                      | 32.1                       | 2.2              | 1.6              | 0.3              |
| 190                                      | 32.5                       | 2.1              | 1.5              | 0.3              |
| 200                                      | 33.0                       | 2.0              | 1.5              | 0.3              |

**Specificatie**

Verlichting

|                                      |   |
|--------------------------------------|---|
| Licht / LED-type                     | White   |
| Aantal leds                          | 8   |
| LED aan / uit schakelbaar:           | Yes   |
| Infrarood filter                     | IR cut-filter >650 nm   |
| Diffusor beschikbaar                 | Yes (N3C-D included)  |
| Emissiefilter                        | No  |
| Polarisator                          | Yes, linear   |
| <b>Optiek</b>                        |   |
| Vergroting                           | 10x~200x  |
| Macro zoom                           | No  |
| Werkafstand                          | Long  |
| Type lens                            | Glass with anti-reflection coating                                    |
| <b>Sensor</b>                        |   |
| Sensortype                           | CMOS  |
| Resolutie                            | 1.3 Megapixel (1280x1024)   |
| Maximale framesnelheid               | 30 fps  |
| <b>Compatibiliteit</b>               |   |
| Interface                            | USB 2.0   |
| Besturingssysteem                    | Windows 7, 8, 10 & 11, MacOS 10.12 and up                             |
| Software                             | DinoCapture 2.0 (Windows), DinoXcope (Mac OS)                         |
| Ondersteunde beeldformaten (Windows) | BMP, GIF, PNG, JPG, TIF, RAS, PNM, TGA, PCX, MNG, WBMP, JP2, JPC, PGX |
| Ondersteunde videoformaten (Windows) | WMV, FLV, SWF   |
| Ondersteunde beeldformaten (MacOS)   | JPEG, PNG   |
| Ondersteunde videoformaten (MacOS)   | MOV   |
| Beeldvormingsnormen                  | DirectShow, UVC   |
| Wifi                                 | Wireless-ready, requires the WF-20 adapter (optional)                 |
| <b>Behuizing</b>                     |   |
| Materiaal van de behuizing           | Composite/ plastic housing  |
| Vergrotingsslot                      | Yes   |
| Afmetingen                           | 11.4cm (L) x 3.3cm (D)  |
| Gewicht                              | 111g  |
| Kabellengte                          | 1.8m  |
| <b>Kenmerken</b>                     |   |
| Bijzonderheid                        | Automatic Magnification Reading (AMR), Flexible LED Control (FLC)     |
| Meting                               | Yes   |

|                          |  |
|--------------------------|--|
| Kalibratie               | Yes  |
| Microtouch-sensor        | Yes  |
| ESD veilig               | No   |
| <b>Informatie</b>        |  |
| Inhoud van de verpakking | Microscope, carry pouch, software CD, calibration target, user manual, N3C-O- Open cap, N3C-C- Closed cap, N3C-D- Diffuser cap, N3C-E- Extension cap, N3C-L- Long cap, N3C-S- Side light cap |
| Garantie-informatie      | 2 years European warranty  |
| Regelgevende goedkeuring | CE, FCC, ROHS  |
| Prijsklasse              | €550,00 - €750,00  |

## **Product galerij**