

# WF7515MZTL

**Merk:** Dino-Lite

**Productcode:** WF7515MZTL



## Korte omschrijving

5 Megapixel resolution  
Robust metal housing  
10-140x magnification  
Long working distance  
Flexible LED Control (FLC)  
Polarizer  
Automatic Magnification Reading (AMR)  
Wireless

## Omschrijving

With the use of the latest, cutting-edge optics, a brand new 5 megapixel sensor and several special features such as Flexible LED Control (FLC) and full aluminum body, the Dino-Lite WF7515MZTL is a marvel of technology and the best choice for the high-demanding professional. The Dino-Lite WF7515MZTL offers superb image quality and color reproduction in a robust, compact and appealing housing.



USB 2.0



Flexible LED  
Control FLC



Continuous  
~10x - 140x



The WF7515MZTL is part of the Long Working Distance (LWD) range and with its Long Working Distance and magnification range from 10 – 140x, it is suitable for a wide range of applications where extra distance to the object or a larger field of view is required.

The extra working distance and larger field of view make this model an ideal solution for tasks such as repair, rework or assembly or for working with bulky or fragile objects that cannot be touched. Because of the built-in polarization filter this model is ideal when working with shiny or reflective objects such as metal, plastic, glass, jewelry, electronics, etc. The AMR function is of particular importance when the measurement functions are frequently used.

**The main features of the WF7515MZTL are:**

- 5 Megapixel Edge sensor
- Long Working Distance (LWD)
- 10-140x magnification
- Integrated polarizer
- Aluminum housing
- Automatic Magnification Reading (AMR)
- Flexible LED Control (FLC)
- Extensive measurement functions
- Calibration
- Exchangeable front caps
- Wireless
- And more...

**Working distance/field of view/depth of field**

MAGNIFICATION RATE	WORKING DISTANCE*	FIELD OF VIEW(X)	FIELD OF VIEW(Y)	DEPTH OF FIELD
<b>Listed values</b>	<b>* Without front</b>			<b>Unit = mm</b>

**may differ  
slightly**

**cap**

10	234.5	39.0	31.2	12
20	112.5	19.5	15.6	4.5
30	72.5	13.0	10.4	3.1
40	54.5	9.8	7.8	1.8
50	43.5	7.8	6.2	1.2
60	37.5	6.5	5.2	0.9
70	33.7	5.6	4.5	0.6
80	31.3	4.9	3.9	0.5
90	29.9	4.3	3.5	0.37
100	29.2	3.9	3.1	0.28
110	29.1	3.5	2.8	0.22
120	29.3	3.3	2.6	0.17
130	29.8	3.0	2.4	0.12
140	30.5	2.8	2.2	0.09

## Specificatie

Verlichting	
Licht / LED-type	White
Aantal leds	8
LED aan / uit schakelbaar:	Yes
Infrarood filter	IR cut-filter >650 nm
Diffusor beschikbaar	Yes (N3C-D included)
Emissiefilter	No
Polarisator	Yes, linear
Optiek	
Vergroting	10-140x
Macro zoom	No
Werkafstand	Long
Type lens	Glass with anti-reflection coating
Sensor	
Sensortype	CMOS
Resolutie	5 Megapixel (2592x1944)
Maximale framesnelheid	30 fps
Compatibiliteit	
Interface	USB 2.0
Besturingssysteem	Windows 7, 8, 10 & 11, MacOS 10.9 and up
Software	DinoCapture 2.0 (Windows), DinoXcope (Mac

	OS)
Ondersteunde beeldformaten (Windows)	BMP, GIF, PNG, JPG, TIF, RAS, PNM, TGA, PCX, MNG, WBMP, JP2, JPC, PGX
Ondersteunde videoformaten (Windows)	WMV, FLV, SWF
Ondersteunde beeldformaten (MacOS)	JPEG, PNG
Ondersteunde videoformaten (MacOS)	MOV (max 1.3MP)
Beeldvormingsnormen	DirectShow, UVC
Wifi	Yes
<b>Behuizing</b>	
Materiaal van de behuizing	Metal housing
Vergrotingsslot	Yes
Afmetingen	10.5cm (L) x 3.2cm (D)
Gewicht	135gr
Kabellengte	1.8m
<b>Kenmerken</b>	
Bijzonderheid	Automatic Magnification Reading (AMR), Flexible LED Control (FLC).
Meting	Yes
Kalibratie	Yes
Microtouch-sensor	Yes
ESD veilig	Yes
<b>Informatie</b>	
Inhoud van de verpakking	Microscope, carry pouch, software CD, calibration target, user manual, N3C-O- Open cap, N3C-C- Closed cap, N3C-D- Diffuser cap, N3C-E- Extension cap, N3C-L- Long cap, N3C-S- Side light cap
Garantie-informatie	2 years European warranty
Regelgevende goedkeuring	CE, FCC, ROHS
Prijsklasse	€1400,00 - €1600,00

## Product galerij

