

WF4515ZTL - Wireless

Marka: Dino-Lite
Ürün Kodu: WF4515ZTL



Short Description

1.3 Megapixel Edge sensor
Long Working Distance (LWD)
Free iOS and Android App
Flexible LED Control (FLC)
Automatic Magnification Reading (AMR)

Açıklama

The Dino-Lite WF4515ZTL is a Wireless model that is part of the Long Working Distance (LWD) series. Go from wireless to wired and back in an instant. Work wired via USB or work wireless with the attachable WF-20 Wireless adapter.



USB 2.0



1,3 Megapixels
1280 x 1024




Adjustable
~10x - 140x




Exchangeable
cap



Long working
distance



Polarizer
anti-reflection



Measurement
functionality



Flexible LED
Control FLC



Automatic
Magnification
Reading (AMR)



The WF4515ZTL is equipped with premium features such as Flexible LED Control (FLC), integrated polarizer, extensive measurement functionality and Automatic Magnification Reading (AMR) for measurement-intensive applications.

De belangrijkste kenmerken van de WF4515ZTL zijn:

- Completely wireless solution (including WF20)
- 1.3 Megapixel Edge sensor
- 10-140x magnification
- Long Working Distance (LWD)
- Automatic Magnification Reading (AMR)
- Adjustable polarizer
- Flexible LED Control (FLC)
- And more ...

Working distance/field of view/depth of field

| Magnification Rate | Working Distance * | Field of View(x) | Field of View(y) | Depth of Field |
|-----------------------------------|---------------------|------------------|------------------|----------------|
| Listed values may differ slightly | * Without front cap | | | Unit = mm |
| 10 | 234.5 | 39.0 | 31.2 | 12 |
| 20 | 112.5 | 19.5 | 15.6 | 4.5 |
| 30 | 72.5 | 13.0 | 10.4 | 3.1 |
| 40 | 54.5 | 9.8 | 7.8 | 1.8 |
| 50 | 43.5 | 7.8 | 6.2 | 1.2 |
| 60 | 37.5 | 6.5 | 5.2 | 0.9 |
| 70 | 33.7 | 5.6 | 4.5 | 0.6 |
| 80 | 31.3 | 4.9 | 3.9 | 0.5 |
| 90 | 29.9 | 4.3 | 3.5 | 0.37 |
| 100 | 29.2 | 3.9 | 3.1 | 0.28 |
| 110 | 29.1 | 3.5 | 2.8 | 0.22 |
| 120 | 29.3 | 3.3 | 2.6 | 0.17 |
| 130 | 29.8 | 3.0 | 2.4 | 0.12 |
| 140 | 30.5 | 2.8 | 2.2 | 0.09 |

Özellikler

| Lighting | |
|-----------------------------------|---|
| Light/ LED type | White |
| Number of LEDs | 8 |
| LED on/off switchable: | Yes |
| Infrared filter | IR cut-filter >650 nm |
| Diffuser available | Yes (N3C-D included) |
| Emission filter | No |
| Polarizer | Yes, linear |
| Optics | |
| Magnification | 10-140x |
| Macro zoom | No |
| Working distance | Long |
| Lens type | Glass with anti-reflection coating |
| Sensor | |
| Sensor type | CMOS |
| Resolution | 1.3 Megapixel (1280x1024) |
| Maximum frame rate | 30 fps |
| Compatibility | |
| Interface | USB 2.0 |
| Operating system | Windows 7, 8, 10 & 11, MacOS 10.11.16 and up |
| Software | DinoCapture 2.0 (Windows), DinoXcope (Mac OS) |
| Supported image formats (Windows) | BMP, GIF, PNG, JPG, TIF, RAS, PNM, TGA, PCX, MNG, WBMP, JP2, JPC, PGX |
| Supported video formats (Windows) | WMV, FLV, SWF |
| Supported image formats (MacOS) | JPEG, PNG |
| Supported video formats (MacOS) | MOV |
| Imaging standards | DirectShow, UVC |
| Wifi | Yes |
| Housing | |
| Housing material | Composite/ plastic housing |
| Magnification lock | Yes |
| Dimensions | 11.4cm (L) x 3.3cm (D) |
| Weight | 111g |
| Cable length | 1.8m |

| Features | |
|----------------------|---|
| Special feature | Automatic Magnification Reading (AMR), Flexible LED Control (FLC) |
| Measurement | Yes |
| Calibration | Yes |
| Microtouch sensor | Yes |
| ESD safe | No |
| Information | |
| Package contents | Microscope, WF-20, carry pouch, software CD, calibration target, user manual, N3C-O- Open cap, N3C-C- Closed cap, N3C-D- diffuser cap, n3c-E- extension cap, N3C-L- Long cap, N3C-S- Side light cap |
| Warranty information | 2 years European warranty |
| Regulatory approval | CE, FCC, ROHS |
| Price range | €900,00 - €1100,00 |

Product Gallery